



HOTLINE II

Description: ENDURAFLEX Black, soft/hard/soft, TRI-BOND natural rubber compounded for high heat and abrasion resistance in continuous service

Durometer of Face Material: Shore A Scale

Pressure Cure: 55 to 65

Atmospheric Cure: 50 to 65

Available Gauges: 3/16", 1/4", 1/2", 4mm, 5mm, & 6mm, & 10mm.

Adhesive System:

Adhesives: ENDURABOND 1*2*3 SYSTEM

1st coat on metal:	Primer #1
2nd coat on metal:	Intermediate #2
3rd coat on metal:	Tack #3
On the rubber:	Tack #3

Skive: Closed

Cure Methods and Times:

Autoclave: 2 Hours @ 275° F (135°C)
Internal Pressure: 12 Hours @ 250° F (122°C)
For vacuum service: 20 to 24 hours @ 250°F (122°C) Depending on atmospheric temperatures and conditions.
Atmospheric: 2 Step process with option for Step 2 Step 1 – 6 hours from ambient to 160°F (71°C) Step 2 – 24 hours at 180°F (82°C) or 20 hours at 200°F (94°C) Atmospheric curing not recommended for vacuum service.

Note: Cure times may require adjustment to compensate for heavy metal thickness, low exterior temperatures or other unusual factors. See Section 14 – Curing Instructions.

Repairs: Repair with original lining or C633BN. See Section 16 – Repair Procedures.

Storage Life:

From 32°F (0°C) to 50°F (10°C)	180 days
From 51°F (13°C) to 65°F (19°C)	90 days
From 66°F (21°C) to 75°F (23°C)	60 days
From 75° F (23°C) to 85° F (30°C)	30 days
Do not exceed 90°F (32°C) prior to use.	Cold storage

Typical Physical Properties:

Tensile Strength – PSI	ASTM D412	2400
% Elongation at break	ASTM D412	600
Durometer	ASTM D2240	65A
Specific Gravity	ASTM D927	1.07
Adhesion to Metal	ASTM D429	30 Lbs.

Application methods shall conform to BLAIR Rubber Company instructions contained in the Engineering & Applicator manual. Deviations from the specifications must be approved by BLAIR Rubber Company.

Notes: Always apply plastic side down against the substrate.

Caution: Soft natural rubber is susceptible to deterioration by sunlight and oxygen called weather checking. **Do not** expose rubber lining to sunlight, ozone or oxygen.

Applicator notes:

1. This lining is susceptible to over cure. Over cure or reversion may occur when heat cure time and temperature parameters when pressure curing are exceeded.
2. The temperature of the substrate must be greater than 60° F (15° C) prior to applying primer and rubber. Temperatures should not exceed 120° F (48° C).